


# Fichier:X252 Forward Clamp Out Sensor Setup Stuertz Infeed Set to Q1.jpg



1	Operating display	green
2	Signal display	yellow
3	TEACH-IN button	
4	Mode rotary switch	
5	Laser output	

Size of this preview:800 × 267 pixels

Original file (835 × 279 pixels, file size: 39 KB, MIME type: image/jpeg)

X252\_Forward\_Clamp\_Out\_Sensor\_Setup\_Stuertz\_Infeed\_Set\_to\_Q1

## File history

Click on a date/time to view the file as it appeared at that time.

	Date/Time	Thumbnail	Dimensions	User	Comment
current	15:18, 26 January 2023		835 × 279 (39 KB)	Gareth Green (talk   contribs)	X252_Forward_Clamp_Out_Sensor_Setup_Stuertz_Infeed_Set_to_Q1

You cannot overwrite this file.

## File usage

There are no pages that link to this file.